

Accessories and special frames for R.O. technique



AquaCare GmbH & Co. KG
Am Wiesenbusch 11 • D-45966 Gladbeck • Germany
☎ 0 20 43 - 37 57 58-0 • 📠 0 20 43 - 37 57 58-90
www.aquacare.de • info@aquacare.de

Special frames / Cabinet units



frame made of stainless steel 1.4301



R.O. unit HP2000 with pressure tank, prefixed duplex softener and mixed bed resin



R.O. unit HP 12,000 with softener (left), storing tank (right) and booster unit DEA500



R.O. unit built in stainless steel cabinet

Water storing and distributing



R.O. unit with pressure tank



pressure less tank with pressure rise unit

Accessories



ultra sonic sensor for salt level of the softener
or
brine float for controlling the brine concentration of a softener



hardness monitor: monitors the hardness of the feed water for a R.O. unit and protects the membranes at hard water alarm



permeate reject valve:
rejects the first bad water after starting the R.O. unit; enlarges the capacity of a down stream installed ultra pure water resin

Mixing valve
with or without flow meter,
with or without conductivity control

Control available as PLC, too

High precisions conductivity meter